THE PROFESSIONAL'S CHOICE SINCE 1953


Master® MH-200V-LPC-A Propane Convection Heater—Variable Output, 200,000 BTU



- Variable BTU to efficiently heat-up well-ventilated spaces construction sites, workshops, farms, or garages
- Made of rugged steel for years of use
- Piezo ignition; no electricity required
- 1-year limited warranty

Product Description

When you choose a Master® propane convection heater, everyone within 5000 square feet with feel the warmth thanks to its efficient 360° heating radius. This powerful space heater delivers long-lasting (up to 31 hours) of electricity-free heat. It's like a bonfire without the open flame – perfect for barns, large warehouses, construction sites and loading docks. As you'd expect from Master, safety and convenience are built in to this durable product. Master – built for power.



©2025 Pinnacle Climate Technologies

Features and Benefits

- Advanced safety features include hightemperature limit shut-off, flame-out fuel cut and a thermocouple
- Piezo ignition and inner wind guard; variable heat settings
- CSA certified for use with 100 lb. propane cylinder; no electricity required
- Heavy-duty steel construction; 2-piece burn chamber design
- 10-ft. LP cylinder hose and regulator included
- 1-year limited warranty

Key Specs

Model Number	MH-200V-LPC-A
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	14
Air Flow (CFM)	100 lb. Propane
Fuel Consumption (lb/hr)	3.2 - 9.3

Max. Operating Hours	31
Heating Area (sq. ft.)	5000
Max. BTU	200,000
Dimensions (L x W x H) (in.)	16 x 16 x 26

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2025 Pinnacle Climate Technologies