

A tough, mid-cut safety boot with highest protection level (S3) and BOA® Fit System built for heavy work.

jalas® HEAVY DUTY 1278

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S3, HRO, CI, HI, FO, SC, LG

Learn more

A tough, mid-cut safety boot with highest protection level (S3) and BOA® Fit System built for heavy work. The PU-coated leather and microfibre upper gives excellent foot protection and additional ankle support. The oil and heat-resistant nitrile outer sole gives excellent grip, and JALAS® Composite Toe Cap, nail protection in steel and double impact protection zones in PORON® XRD® mean safer workdays.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Heat-resistant outsole
- Oil-resistant outsole
- TPU heel support
- Bellows tongue
- Padded shaft edge in memory foam
- BOA® Fit System
- Ankle support
- Pull loops
- Water repellent
- Ergonomically shaped
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

BOA DIALED IN. PRECISION FIT. Xrd PROTECTION LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Sprain injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, All-year use, Warm surfaces, Environments with risk for outsole penetration, Oily and greasy environments, Dirty environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Regular
COLLECTION Heavy Duty
UPPER MATERIAL PU-coated leather
PRONOSE MATERIAL PU
TOECAP MATERIAL Composite
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8217 FX2 Climate
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.4 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S3, HRO, CI, HI, FO, SC, LG

FEATURES

- Anti-static properties
- Composite toecap
- Ergothan Shock Absorption System
- ESD
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	1278-35	6408487506086
36	3	4	5	1278-36	6408487506093
37	4	5	6	1278-37	6408487506109
38	5	5.5	6.5	1278-38	6408487506116
39	6	6.5	7.5	1278-39	6408487506123
40	6.5	7.5	8.5	1278-40	6408487506130
41	7	8	9	1278-41	6408487506147
42	8	9	10	1278-42	6408487506154
43	9	9.5	11	1278-43	6408487506161
44	10	10.5	11.5	1278-44	6408487506178
45	10.5	11	12.5	1278-45	6408487506185
46	11	12	13	1278-46	6408487506192
47	12	13	14	1278-47	6408487506208
48	13	13.5	14.5	1278-48	6408487506215

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.