
Master MHD-30W 30" High Velocity Heavy Duty Wall Fan
7550 CFM, 1/4 HP, 120 Volt



- Great for garages, barns, warehouses, or assembly plants
- All-metal heavy duty construction
- Direct-drive motor with airflow up to 7550 CFM
- 1/4 HP industrial motor
- OSHA-compaliant safety guards
- 3 variable speed settings
- Easy installation with included wall mount
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading, 30" High Velocity Heavy Duty Wall Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting all-metal construction. Plus, the convenient wall mount gives you unrivaled versatility for all your cooling needs. Whether you're in the barn, relaxing at home, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. Master – built for power.



©2026 Pinnacle Climate Technologies

Features and Benefits

- Great for garages, barns, warehouses, or assembly plants
- All-metal heavy duty construction
- Direct-drive motor with airflow up to 7550 CFM
- 1/4 HP industrial motor
- OSHA-compaliant safety guards
- 3 variable speed settings
- Easy installation with included wall mount
- 1-year limited warranty

Key Specs

Model Number	MHD-30W
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	47
Air Flow (CFM)	7550 / 6800 / 5800
Motor Size (HP)	1/4
Variable Speed	Yes
Volts	120
Amps	1.7
Product Dimensions (L x W x H) (in.)	40 x 8 x 36

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2026 Pinnacle Climate Technologies

03/13/2026