ABB BALDOR RELIANCE

Customer information packet

VL3515

2HP, 3450RPM, 1PH, 60HZ, 56C, 3535L, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:02:19 PM

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	2.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	115.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	11.500 A @ 230.0 V
	12.000 A @ 208.0 V
	23.000 A @ 115.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	74.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	BE
Type	AC
Mech. spec.	35C013
Base	
Status	PRD/A
Elec. spec.	35WG0506
Layout	35LYC013
Eff. date	01-13-2026
CD Diagram	CD0001
Poles	02
Leads	4#14 A PH,2#18 B PH
Proprietary	False
Created date	06-21-2007

High Voltage Full Load Amps	11.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	4 @ 14 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3535L
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.12 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	VL3515										
SPEC.	35C13-506										
HP	2										
VOLTS	115/208-230										
AMP	23/12-11.5										
RPM	3450										
FRAME	56C		**HZ**	60			**PH**	1			
SER.F.	1.15	**CODE**	K	**DES**	L	**CLASS**	F				
NEMA-NOM-EFF	74	**PF**	82								
RATING	40C AMB-CONT										
CC											
DE	6205		**ODE**	6203							
ENCL	TEFC	**SN**									

AC Induction Motor Performance Data
Record # 8075
Typical performance - not guaranteed values

Winding: 35WG0506-R007	**Type:** 3535L	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	3 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			23/12-11.5	**Breakdown Torque**	9 LB-FT
R.P.M.			3450	**Pull-up Torque**	6 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	7.5 LB-FT
NEMA Design Code	L	**KVA Code**	K	**Starting Current**	78 A
Service Factor (S.F.)			1.15	**No-load Current**	6 A
NEMA Nom. Eff.	74	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.864 Ω A Ph 1.26 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	82°C
S.F. Amps				**Temp. Rise @ S.F. Load**	91°C

Load Characteristics 230 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	50	65	75	81	85	87	83
Efficiency	49.1	64.2	70.5	73.4	74.3	74.1	73.9
Speed	3569	3548	3524	3499	3471	3438	3482
Line amperes	6.65	7.75	9.2	10.9	12.9	15.1	12.1


ABB Motors and Mechanical Inc.


WINDING # 35WG0506

2 HP 1 PH 60 HZ 3450 RPM 230 V 3535L


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=9 PU=6 LR=7.5 LRA=78




35LYC013
510-520 = 12.22
521-528 = 13.23
529-535 = 14.10
536-546 = 15.47
2.06
.13
1.88
.19 KEY
1.38 LONG
Ø7.19
NAMEPLATE
Ø 4.500
4.497
Ø6.49
Ø .6250
.6245
3.75
6.61
5.71
4.18
45°
45°
5.55
THERMAL
(WHEN REQ'D)
4 HOLES
.38-16 TAP
ON 5.88 DIA. B.C.
LEAD HOLE
Ø .88
4.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.
REV. DESC: UPDATE 3D MODEL BOM PER REV AC, NO CHG TO 2D PRINT
REV: N
VERSION: 06
REVISED: 09:42:56 04/07/2022
TDR: 000001188385
MODEL NO: 35LYC013
REF: -
BY: USBUFRA
Material: -
B
BALDOR - RELIANCE®
STD VERT 56C TEFC 35L
SH 1 of 1
35LYC013

CD0001



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0001

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
CD0001		FILE: AAA00007405	MDL: –
		MTL: –	TYPE L, DV, REV, 6 LEADS