



Safety Data Sheet

Copyright, 2025, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group: 44-3853-7
Issue Date: 03/24/25

Version Number: 2.00
Supersedes Date: 10/03/24

SECTION 1: Identification

1.1. Product identifier

3M™ Abrasive Products, Cubitron™ 3 Fibre Disc, 1182C, TN and GL Attachment, Slotted

1.2. Recommended use and restrictions on use

Recommended use

Abrasive Product, For industrial/occupational use only. Not for consumer sale or use.

1.3. Supplier's details

MANUFACTURER: 3M
DIVISION: Abrasive Systems Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000, USA
Telephone: 1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

2.2. Label elements

Signal word

Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

14% of the mixture consists of ingredients of unknown acute dermal toxicity.

34% of the mixture consists of ingredients of unknown acute inhalation toxicity.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
------------	------------	---------

Fibre Backing	Mixture	40 - 80 Trade Secret *
Ceramic Aluminum Oxide Mineral (non-fibrous)	1344-28-1	5 - 25 Trade Secret *
Inorganic Fluoride 1	13775-53-6	5 - 20 Trade Secret *
Cured Resin	Mixture	5 - 15 Trade Secret *
Filler	1317-65-3	1 - 5 Trade Secret *
Inorganic Fluoride 2	7789-75-5	< 5 Trade Secret *
Steel or Plastic Attachment	Mixture	<= 5 Trade Secret *
Titanium Dioxide	13463-67-7	< 0.5 Trade Secret *

*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

Do not induce vomiting. Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No critical symptoms or effects. See Section 11.1, information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

Material will not burn. Use a fire fighting agent suitable for the surrounding fire.

5.2. Special hazards arising from the substance or mixture

Exposure to extreme heat can give rise to thermal decomposition.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide
Carbon dioxide

Condition

During Combustion
During Combustion

5.3. Special protective actions for fire-fighters

Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Use personal protective equipment based on the results of an exposure assessment. Refer to Section 8 for

PPE recommendations. If anticipated exposure resulting from an accidental release exceeds the protective capabilities of the PPE listed in Section 8, or are unknown, select PPE that offers an appropriate level of protection. Consider the physical and chemical hazards of the material when doing so. Examples of PPE ensembles for emergency response could include wearing bunker gear for a release of flammable material; wearing chemical protective clothing if the spilled material is a corrosive, a sensitizer, a significant dermal irritant, or can be absorbed through the skin; or donning a positive pressure supplied-air respirator for chemicals with inhalation hazards. For information regarding physical and health hazards, refer to sections 2 and 11 of the SDS.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Do not breathe thermal decomposition products. For industrial/occupational use only. Not for consumer sale or use. Avoid breathing of dust created by sanding, grinding or machining. Damaged product can break apart during use and cause serious injury to face or eyes. Check product for damage such as cracks or nicks prior to use. Replace if damaged. Always wear eye and face protection when working at sanding or grinding operations or when near such operations. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Solids can generate static electricity charges when transferred and in mixing operations sufficient to be an ignition source. Evaluate the need for precautions, such as grounding and bonding, low energy transfer of material (e.g. low speed, short distance), or inert atmospheres.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Filler	1317-65-3	OSHA	TWA(as total dust):15 mg/m ³ ;TWA(respirable fraction):5 mg/m ³	
Particles (insoluble or poorly soluble) not otherwise specified, inhalable particles	1317-65-3	ACGIH	TWA(inhalable particulates):10 mg/m ³	
Particles (insoluble or poorly soluble) not otherwise specified, respirable particles	1317-65-3	ACGIH	TWA(respirable particles):3 mg/m ³	
Ceramic Aluminum Oxide Mineral (non-fibrous)	1344-28-1	OSHA	TWA(as total dust):15 mg/m ³ ;TWA(respirable fraction):5 mg/m ³	
Particles (insoluble or poorly soluble) not otherwise specified, inhalable particles	1344-28-1	ACGIH	TWA(inhalable particulates):10 mg/m ³	
Particles (insoluble or poorly soluble) not otherwise specified,	1344-28-1	ACGIH	TWA(respirable particles):3 mg/m ³	

respirable particles				
Titanium Dioxide	13463-67-7	ACGIH	TWA(Respirable nanoscale particles):0.2 mg/m3;TWA(Respirable finescale particles):2.5 mg/m3	A3: Confirmed animal carcin.
Titanium Dioxide	13463-67-7	OSHA	TWA(as total dust):15 mg/m3	
FLUORIDES	13775-53-6	ACGIH	TWA(as F):2.5 mg/m3	A4: Not class. as human carcin
FLUORIDES	13775-53-6	OSHA	TWA(as F):2.5 mg/m3;TWA(as dust):2.5 mg/m3	
FLUORIDES	7789-75-5	ACGIH	TWA(as F):2.5 mg/m3	A4: Not class. as human carcin
FLUORIDES	7789-75-5	OSHA	TWA(as F):2.5 mg/m3;TWA(as dust):2.5 mg/m3	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

For those situations where the material might be exposed to extreme overheating due to misuse or equipment failure, use with appropriate local exhaust ventilation sufficient to maintain levels of thermal decomposition products below their exposure guidelines. Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

Skin/hand protection

Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

Respiratory protection

Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure.

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

For those situations where the material might be exposed to extreme overheating due to misuse or equipment failure, use a positive pressure supplied-air respirator.

Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state

Solid

Color

Purple

Odor

Slight Polymeric

Odor threshold

Not Applicable

pH

Not Applicable

Melting point

Not Applicable

Boiling Point

Not Applicable

Flash Point

Not Applicable

Evaporation rate

Not Applicable

Flammability (solid, gas)

Not Classified

Flammable Limits(LEL)

Not Applicable

Flammable Limits(UEL)

Not Applicable

Vapor Pressure

Not Applicable

Vapor Density

Not Applicable

Density

Not Applicable

Specific Gravity

Not Applicable

Solubility In Water

Not Applicable

Solubility- non-water

Not Applicable

Partition coefficient: n-octanol/ water

Not Applicable

Autoignition temperature

Not Applicable

Decomposition temperature

Not Applicable

Viscosity

Not Applicable

Molecular weight

Not Applicable

Volatile Organic Compounds

Not Applicable

Percent volatile

Not Applicable

VOC Less H₂O & Exempt Solvents

Not Applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

Substance

Hydrogen Fluoride

Condition

At Elevated Temperatures

Refer to section 5.2 for hazardous decomposition products during combustion.

Extreme heat arising from situations such as misuse or equipment failure can generate hydrogen fluoride as a decomposition product.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Ingestion:

No health effects are expected.

Carcinogenicity:

Ingredient	CAS No.	Class Description	Regulation
Titanium dioxide	13463-67-7	Grp. 2B: Possible human carc.	International Agency for Research on Cancer

Additional Information:

This document covers only the product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered. This product contains titanium dioxide. Cancer of the lungs has been observed in rats that inhaled high levels of titanium dioxide. No exposure to inhaled titanium dioxide is expected during the normal handling and use of this product. Titanium dioxide was not detected when air sampling was conducted during simulated use of similar products containing titanium dioxide. Therefore, the health effects associated with titanium dioxide are not expected during the normal use of this product.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Inhalation-Dust/Mist(4 hr)		No data available; calculated ATE >12.5 mg/l
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Ceramic Aluminum Oxide Mineral (non-fibrous)	Dermal		LD50 estimated to be > 5,000 mg/kg
Ceramic Aluminum Oxide Mineral (non-fibrous)	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 2.3 mg/l
Ceramic Aluminum Oxide Mineral (non-fibrous)	Ingestion	Rat	LD50 > 5,000 mg/kg
Inorganic Fluoride 1	Dermal	Rabbit	LD50 > 2,100 mg/kg
Inorganic Fluoride 1	Inhalation-Dust/Mist (4 hours)	Rat	LC50 4.5 mg/l
Inorganic Fluoride 1	Ingestion	Rat	LD50 > 5,000 mg/kg
Filler	Dermal	Rat	LD50 > 2,000 mg/kg
Filler	Inhalation-Dust/Mist (4 hours)	Rat	LC50 3 mg/l
Filler	Ingestion	Rat	LD50 6,450 mg/kg
Inorganic Fluoride 2	Dermal	Professional judgement	LD50 estimated to be 2,000 - 5,000 mg/kg
Inorganic Fluoride 2	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 5.07 mg/l
Inorganic Fluoride 2	Ingestion	Rat	LD50 > 2,000 mg/kg
Titanium Dioxide	Dermal	Rabbit	LD50 > 10,000 mg/kg
Titanium Dioxide	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 6.82 mg/l
Titanium Dioxide	Ingestion	Rat	LD50 > 10,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Ceramic Aluminum Oxide Mineral (non-fibrous)	Rabbit	No significant irritation
Inorganic Fluoride 1	Multiple animal species	No significant irritation
Filler	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Ceramic Aluminum Oxide Mineral (non-fibrous)	Rabbit	No significant irritation
Inorganic Fluoride 1	Rabbit	Mild irritant
Filler	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation

Skin Sensitization

Name	Species	Value
Titanium Dioxide	Human and animal	Not classified

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Ceramic Aluminum Oxide Mineral (non-fibrous)	In Vitro	Not mutagenic
Titanium Dioxide	In Vitro	Not mutagenic
Titanium Dioxide	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
Ceramic Aluminum Oxide Mineral (non-fibrous)	Inhalation	Rat	Not carcinogenic
Titanium Dioxide	Ingestion	Multiple animal species	Not carcinogenic
Titanium Dioxide	Inhalation	Rat	Carcinogenic

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Filler	Ingestion	Not classified for development	Rat	NOAEL 625 mg/kg/day	premating & during gestation

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Filler	Inhalation	respiratory system	Not classified	Rat	NOAEL 0.812 mg/l	90 minutes

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Ceramic Aluminum Oxide Mineral (non-fibrous)	Inhalation	pneumoconiosis	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure
Ceramic Aluminum Oxide Mineral (non-fibrous)	Inhalation	pulmonary fibrosis	Not classified	Human	NOAEL Not available	occupational exposure
Inorganic Fluoride 1	Inhalation	bone, teeth, nails, and/or hair	Causes damage to organs through prolonged or repeated exposure	Rat	NOAEL 0.0005 mg/l	5 months
Inorganic Fluoride 1	Inhalation	respiratory system	Causes damage to organs through prolonged or repeated exposure	Rat	NOAEL 0.00021 mg/l	90 days
Inorganic Fluoride 1	Ingestion	bone, teeth, nails, and/or hair	Causes damage to organs through prolonged or repeated exposure	Rat	LOAEL 0.58 mg/kg/day	14 weeks
Filler	Inhalation	respiratory system	Not classified	Human	NOAEL Not available	occupational exposure
Titanium Dioxide	Inhalation	respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	LOAEL 0.01 mg/l	2 years
Titanium Dioxide	Inhalation	pulmonary fibrosis	Not classified	Human	NOAEL Not available	occupational exposure

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

The substrate that was abraded must be considered as a factor in the disposal method for this product. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Combustion products will include HF. Facility must be capable of handling halogenated materials.

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Not applicable

Health Hazards

Not applicable

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
Ceramic Aluminum Oxide Mineral (non-fibrous)	1344-28-1	Trade Secret 5 - 25

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 3 **Flammability:** 0 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

The NFPA Health code of 3 is due to emergency situations where the material may thermally decompose and release Hydrogen Fluoride. During normal use conditions, please reference Section 2 and Section 11 of the SDS for additional health hazard information.

Document Group: 44-3853-7

Version Number: 2.00

Issue Date: 03/24/25

Supersedes Date: 10/03/24

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com