

Master MH-80V-LPC-A 80,000 BTU LP Convection Heater - Variable Output



- Perfect for large spaces, this propane heater outdoor provides reliable heating while prioritizing user safety
- Single-handed piezo ignition and inner wind guard; variable heat settings
- CSA certified for use with 20 lb. or 100 lbs. propane cylinder; no electricity required
- Heavy-duty steel construction; 2-piece burn chamber design
- 10-ft. LP cylinder hose and regulator included

Product Description

When you choose a Master® propane convection heater, everyone within 1,800 square feet will feel the warmth thanks to its efficient 360° heating radius. This powerful space heater delivers long-lasting (up to 36 hours), electricity-free heat. It's like a bonfire without the open flame—perfect for barns, large warehouses, construction sites and loading docks. As you'd expect from Master, safety and convenience are built in to this durable product. **Master – built for power.**



Key Specs

Model Number	MH-80V-LPC-A	Max. Operating Hours	36
Brand	Master	Heating Area (sq. ft.)	1,800
Warranty	1-year limited warranty	Fuel Consumption (lb/hr)	2.8 / 3.2 / 3.7
Net Weight (lb.)	13	Max. BTU	80,000
Fuel Tank Capacity	100 lb. Propane Tank - Not Included	Dimensions (L x W x H) (in.)	16 x 16 x 22
Fuel Type	Propane	Heater Type	Convection

