ZINSSER®
STAIN KILLING PRIMER SPRAY

DESCRIPTION AND USES

Zinsser® Stain Killing Spray Primer is an all-purpose primer that kills stains from water, fire, smoke, nicotine, tannin bleed, sap steaks, grease, handprints, and more. This oil base aerosol provides dependable stain blocking power, sealing capabilities, and enhances adhesion to slick surfaces.

Zinsser Stain Killing Spray Primer is equipped with an easy-use trigger nozzle that allows more control and creates a smooth and even HVLP like finish. Use to prime all types of bare or painted interior surfaces including wood, drywall, plaster, masonry, metal and PVC. It can be sprayed in any direction. Great for cabinets, furniture, picture frames, stools, benches, arts & crafts, wicker & louvers, and more.

PRODUCT FEATURES AND BENEFITS

- Stops stains from bleeding into topcoat paint
- Precision control tip for smooth and even finish
- Spray in any direction
- Dries fast

PRODUCT

SKU	DESCRIPTION (13 oz. Aerosol)
378493	Stain Killing Primer

PRODUCT APPLICATION

SURFACE PREPARATION

Remove loose paint and rust with a wire brush or sandpaper. Lightly sand glossy surfaces. Clean with soap and water, rinse and let dry.

WARNING! If you scrape, sand or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH-Approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

PRODUCT APPLICATION (cont.)

APPLICATION

Use outdoors or in a well-ventilated area such as an open garage. Use when temperature is between 50°F and 90°F (10-32°C) and humidity is below 65% to ensure proper drying. Do not apply to surfaces that, when heated, exceed 200°F (93°C) or galvanized metal. Avoid spraying in very windy, dusty conditions. Cover surrounding area to protect from spray mist.

Shake can vigorously for one minute after mixing ball begins to rattle. If mixing ball fails to rattle DO NOT STRIKE CAN. Contact Rust-Oleum. Prior to use, slide off the red safety clip from the trigger. Shake often during use. Hold can upright 8-10” from surface and spray in a steady back-and-forth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. For best results, apply multiple light coats versus one heavy coat.

DRY TIME

Can be topcoated in 30 minutes or more based on 70°F-50% relative humidity. Allow more time at cooler temperatures.

CLEAN-UP

When finished spraying, wipe off tip before storing. Clean up wet paint with Xylol or mineral spirits. Dispose of empty can in recycle pickup. Do not burn or place in home trash compactor.

LIMITATIONS

Zinsser Stain Killing Primer will permanently kill existing stains. It will not remove stains subsequent to application. It’s not a disinfectant or sanitizer.

Form: ARJ-2251
Rev.: 041923

ZINSSER®
STAIN KILLING PRIMER SPRAY

PHYSICAL PROPERTIES

		STAIN KILLING PRIMER SPRAY
Resin Type		Alkyd/Solvent-Based
Pigment Type		Inorganic
Solvents		Mineral Spirits, VM&P Naptha, Acetone
MIR		1.00 Max
Fill Weight		13 ounces
Recommended Dry Film Thickness (DFT) per Coat		1.5-2.5 mils (37.5-62.5µ)
Practical Coverage at Recommended DFT (assume 15% material loss)		10-12 sq. ft./can (0.9-1.1 m^2/can) depending on application method and surface porosity
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity	**Touch**	10 minutes
	Handle	20 minutes
	Recoat	30 minutes
Shelf Life		5 years
Flash Point		141°F (-96°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.