ABB BALDOR RELIANCE

Customer information packet

ECP3774T

10HP, 1760RPM, 3PH, 60HZ, 215T, 0748M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:52:34 PM

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.3
Current @ Voltage	25.000 A @ 230.0 V
	12.500 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features

Part Detail

Revision	AD
Type	AC
Mech. spec.	07K374
Base	
Status	PRD/A
Elec. spec.	07WGX776
Layout	07LYK374
Eff. date	10-01-2025
CD Diagram	CD0005
Poles	04
Leads	9#14 Y
Proprietary	False
Created date	08-18-2006

Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.50 IN
Power Factor	82
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1760 rpm
Speed Code	Single Speed

Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257								
CAT.NO.	ECP3774T							
SPEC.	07K374X776G1							
HP	10 TE							
VOLTS	230/460							
AMP	25/12.5							
RPM	1760							
FRAME	215T	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	H	**DES**	A	**CL**	F	
RATING	40C AMB-CONT							
SN								
DE	6307	**ODE**	6307					
NEMA-NOM-EFF	92.4	**PF**	82					
G.MIN.EFF	91.0	**CC**	010A					
T. CODE	T3C	**T=**	160					

NP3260					
SPEC.	07K374X776G1				
D.E. BRG.	35BC03XP30X				
O.D.E. BRG.	35BC03XP30X				
GREASE	POLYREX EM				
RPM MAX	2700	**MAX. KVAR**	1.7		
BLANK					
INV.TYPE	PWM				
T=	160				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	1.3	**CT HZ TO**	60		
VT HZ FROM	0-	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			

Accessories

Part number	Description	Multiplier
37-1304	C FACE KIT	A8

AC Induction Motor Performance Data
Record # 25097
Typical performance - not guaranteed values

Winding: 07WGX776-R016	**Type:** 0748M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25/12.5	**Breakdown Torque**	87 LB-FT
R.P.M.			1760	**Pull-up Torque**	51.9 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	57.5 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	88.5 A
Service Factor (S.F.)			1.15	**No-load Current**	5.12 A
NEMA Nom. Eff.	92.4	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.973 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
S.F. Amps				**Temp. Rise @ S.F. Load**	76°C
				Locked-rotor Power Factor	35
				Rotor inertia	1.18 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	44	67	78	82	84	85	83
Efficiency	90	92.9	93.1	92.5	91.4	90.1	91.8
Speed	1790	1781	1771	1762	1750	1739	1755
Line amperes	5.84	7.52	9.75	12.3	15.2	18.3	14


ABB Motors and Mechanical Inc.


WINDING # 07WGX776

10 HP 3 PH 60 HZ 1760 RPM 460 V 0748M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=87 PU=51.9 LR=57.5 LRA=88.5




07LYK374
717-750 = 19.49
9.11
3.88
3.38
AUXILIARY NP
(WHEN REQ'D)
PLUG
Ø12.19
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
FORSHEDA
SLINGER
SLINGER
GROUND
LUG
8 HOLES
Ø.41
DRAIN
FITTING
(EA. END)
5.50
5.50
.57
7.00
3.51
8.13
14.62
8.87
5.75
2.04
5.74
5.25
5.19
LEAD
HOLE
1.00 N.P.T.
4.25
4.25
7.25
4.82
9.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRAWING TO SWD
REV: G
VERSION: 07
REVISED: 11:34:04 11/21/2022
TDR: 000001199231
MODEL NO. 07LYK374
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5T TEFC M CP W/6307 BRGS, LIPPED KOBX LID
07LYK374

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS