



jalas® HEAVY DUTY 1358

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S3L, HRO, M, CI, FO, SC

Learn more

A tough, water-repellent mid-cut safety boot featuring highest (S3) protection with unique BOA® Fit System. PU-coated leather and microfibre upper has excellent foot support and certified ankle impact protection. Integrated impact protection of the metatarsal part of the foot. An oil and heat-resistant Vibram Arctic Grip outer sole gives steady feet in slippery conditions. JALAS® Composite Toe Cap, plasma-treated puncture protection and double impact protection zones in PORON® XRD®.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Metatarsal protection with integrated PORON® XRD®
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Polstered shaft edge
- BOA® Fit System
- Ankle protection
- Ankle support
- Pull loops
- Airport friendly
- Arctic Grip traction outsole
- ESD
- Water repellent
- Ergonomically shaped
- Reflector
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Sprain injuries, Antistatic, Slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, All-year use, Metal-free requirements for shoes, Warm surfaces, Environments with risk for outsole penetration, Slippery environments, Dry environments, Cold environments, Moist environments, Oily and greasy environments, Dirty environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Heavy Duty
UPPER MATERIAL PU-coated leather, Microfiber
PRONOSE MATERIAL PU
TOECAP MATERIAL Composite
LINING MATERIAL Technical fleece
INSOLE JALAS 8217 FX2 Climate
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Arctic Grip traction outsole (HNBR rubber + gripper lugs)
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.67 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC TP TC 019:2011

EN ISO 20345:2022
S3L, HRO, M, CI, FO, SC

FEATURES

- Anti-static properties
- Composite toecap
- Ergothan Shock Absorption System
- ESD
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in plasma-treated composite (PTC) textile
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	1358-35	6408487511950
36	3	4	5	1358-36	6408487509407
37	4	5	6	1358-37	6408487509414
38	5	5.5	6.5	1358-38	6408487509421
39	6	6.5	7.5	1358-39	6408487509438
40	6.5	7.5	8.5	1358-40	6408487509445
41	7	8	9	1358-41	6408487509452
42	8	9	10	1358-42	6408487509469
43	9	9.5	11	1358-43	6408487509476
44	10	10.5	11.5	1358-44	6408487509483
45	10.5	11	12.5	1358-45	6408487509490
46	11	12	13	1358-46	6408487509506
47	12	13	14	1358-47	6408487509513
48	13	13.5	14.5	1358-48	6408487509520

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.