ABB BALDOR RELIANCE

Customer information packet

CFDL3516TM

2HP, 1740RPM, 1PH, 60HZ, 56CHZ, 3534LC, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:27:45 PM

Specifications

Enclosure	TEFC
Frame	56CHZ
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	2.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	CURUS
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.200 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	8.2 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs

Part Detail

Revision	A
Type	AC
Mech. spec.	35E2321
Base	
Status	PRD/A
Elec. spec.	35WGG819
Layout	35LYE2321
Eff. date	01-07-2025
CD Diagram	CD0002A02
Poles	04
Leads	2#16 A PH,3#18 B&J
Proprietary	False
Created date	12-13-2024

Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	2 @ 16 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3534LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.10 IN
Power Factor	99
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	KO
Winding Thermal 2	None

Nameplate

NP1280L										
CAT.NO.	CFDL3516TM									
SPEC.	35E2321G819									
HP	2									
VOLTS	230									
AMP	8.2									
RPM	1740									
FRAME	56CHZ	**HZ**	60		**PH**	1				
SER.F.	1.15	**CODE**	J	**DES**	L		**CL**	F		
NEMA-NOM-EFF	78	**PF**	99							
RATING	40C AMB-CONT									
CC										
DE	6205	**ODE**	6203							
ENCL	TEFC	**SN**								
	SFA 9.46									

AC Induction Motor Performance Data
Record # 108662
Typical performance - not guaranteed values

Winding: 35WGG819-R002	**Type:** 3534LC	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			2	**Full Load Torque**	6.05 LB-FT
Volts			230	**Start Configuration**	direct on line
Full Load Amps			8.2	**Breakdown Torque**	17.5 LB-FT
R.P.M.			1740	**Pull-up Torque**	12 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	19.1 LB-FT
NEMA Design Code	L	**KVA Code**	J	**Starting Current**	65.2 A
Service Factor (S.F.)			1.15	**No-load Current**	2.03 A
NEMA Nom. Eff.	78	**Power Factor**	99	**Line-line Res. @ 25ºC**	1.6721 Ω A Ph 3.8548 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	80°C
S.F. Amps				**Temp. Rise @ S.F. Load**	93°C

Load Characteristics 230 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	97	99	99	99	99	99	99
Efficiency	52.1	70.1	77.3	79.8	79.5	77.4	79.6
Speed	1785.1	1773.1	1758.2	1743.1	1722.5	1698.8	1731
Line amperes	3.29	4.71	6.38	8.19	10.3	12.7	9.46


ABB Motors and Mechanical Inc.


WINDING # 35WGG819

2 HP 1 PH 60 HZ 1740 RPM 230 V 3534LC

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=17.5 PU=12 LR=19.1 LRA=65.2





PULLEY END DETAIL

FARM DUTY MOTOR

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: UPDATE 3D MODEL BOM PER REV D, NO CHG TO 2D PRINT			
REV: D	VERSION: 04	REVISED: 03:24:06 04/01/2022	TDR: 000001188385
MODEL NO. 35LYE2321			REF: -
BY: USBUFRA			B

BALDOR - RELIANCE®

HOR 56CHZ TEFC LC,1"MTO KO BOX FARM DUTY,W/SEAL,SEALED BRGS
SH 1 of 1

35LYE2321

CD0002A02



	LINE A	LINE B	JOIN
STD	1,8	4	J,5
OPP	1,5	4	J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE 2–TERMINAL THERMAL DETAIL, SEE CD0002A04			BALDOR ELECTRIC Co.
REV. LTR: D	VERSION: 01	TDR: 000000360649	
CD0002A02	FILE: \AAA\00007\520	REVISED: 17:11:40 04/15/2005	TYPE LC, SV, REV, THERMAL, 5 LEADS
	MTL: –	BY: ENJOEP0	

CD0002A02