



TEGERA® 666

Learn more

KNITTED FLAME RETARDANT DIPPED GLOVE

Knitted flame-retardant glove that withstands contact heat up to 100°C/212°F, with a neoprene palm coating for a secure grip. Ideal for assembly work that demands both cut and heat protection. Additionally, it features a water and oil-repellent palm and is knitted with 13 gg para-aramid thread.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Flexible
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Water and oil repellent palm
- Flame retardant
- Heat-resistant

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Cut injuries, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Warm environments, Dirty environments

PRIMARY AREAS OF USE

Machine operating, Sheet-metal work, Construction, Metalwork, Hot work, Glass industry work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL Glass fibre thread, Para-aramid
LENGTH 220-260 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bag with euro slot
DIPPING Palm-dipped
DIPPING MATERIAL Neoprene
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 10.7 N
INNER MATERIAL SPECIFICATION Para-aramid, Glass fibre thread
OUTER MATERIAL SPECIFICATION Chloroprene

COMPLIANCE

CE Cat. II
EN ISO 21420:2020

EAC
TP TC 019:2011

EN 388:2016+A1:2018
2X41C

EN 407:2020
41310X

ANSI A3 CUT

ANSI 3 ABR

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	666-6	7340118462790
7	S	666-7	7392626074101
8	M	666-8	7392626074125
9	L	666-9	7392626074149
10	XL	666-10	7392626074064
11	XXL	666-11	7392626074088

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.