

▲ WARNING

ENG - Do not begin to install product until you have read and understood the instructions and warnings contained in this user guide. This product is designed to be installed on wood stud walls. Hardware is included for wood stud installation. Before installing make sure the supporting surface will support the combined load of the equipment and hardware. Screws must be tightly secured. Do not overtighten screws or damage can occur and product may fail. Always use an assistant or mechanical lifting equipment to safely lift and position equipment. This product is intended for indoor use only. Use of this product outdoors could lead to product failure or personal injury. To reduce the risk of electric shock or fire, do not expose product to water or moisture. Be sure power cord is routed so that it will not be tripped on, stepped on, or pinched by heavy items. Avoid overloading electrical outlets or extension cords. Always disconnect the power cord from the power outlet when installing, servicing, or not using the product for an extended period of time. Do not block ventilation slots or fan exhaust on product. Blocking airflow could damage product. Arrange product to allow air to flow freely around product. Keep product away from direct sunlight or any source of heat. For support please call 1-800-865-2112.


ENG Symbols



ENG WARNING





ENG Screws must get at least three full turns and fit snug.



ENG Do not overtighten screws.


ENG Tools Needed for Assembly.









ENG Parts (Before beginning, make sure you have all parts shown below).

Parts List		KIL740	KIL742	KIL743	KIL746	KIL747
Description	Qty	KIL740-S	KIL742-S	KIL743-S	KIL746-S	KIL747-S
		Part #	Part #	Part#	Part #	Part #
A back assembly	1	150-T1685	150-T1686	150-T1686	150-T1683	150-T1684
B M5 x 12mm pan phl screw	4	520-1027	520-1027	520-1027	520-1027	520-1027
C M5 X 25mm pan phl screw	4	520-9543	520-9543	520-9543	520-9543	520-9543
D M6 x 12mm pan phl screw	4	520-1128	520-1128	520-1128	520-1128	520-1128
E M6 x 25mm pan phl screw	4	520-1208	520-1208	520-1208	520-1208	520-1208
F M8 x 12mm pan phl screw	4	520-9571	520-9571	520-9571	520-9571	520-9571
G M8 x 25mm pan phl screw	4	520-1031	520-1031	520-1031	520-1031	520-1031
H M5/M4/M6 multi washer	4	580-1398	580-1398	580-1398	580-1398	580-1398
I 1/4"spacer	4	540-1059	540-1059	540-1059	540-1059	540-1059
J M5 x 20mm skt screw	2	520-1065	520-1065	520-1065	520-1065	520-1065
K 4mm allen wrench	1	560-9646	560-9646	560-9646	560-9646	560-9646
L front cover BLK front cover SLV	1	150-P1576P 150-4576P	150-P1578P 150-4578P	151-P1609 151-4609	150-P1574P 150-4574P	150-P1575P 150-4575P
M #14 x 2.5" wood screw	4	5S1-015-C03	5S1-015-C03	5S1-015-C03	5S1-015-C03	5S1-015-C03
N adaptor bracket	2	150-T1682	150-T1682	150-T1682	150-T1682	150-T1682
O power strip	1	600-0370	600-0370	600-0370	600-0370	600-0370
P cable tie	6	560-1756	560-1756	560-1756	560-1756	560-1756
Q concrete anchor (not used)	4	590-0320	590-0320	590-0320	590-0320	590-0320











Parts List		KIL748	KIL749	KIL755
Description	Qty	KIL748-S	KIL749-S	KIL755-S
		Part #	Part #	Part#
A back assembly	1	150-T1687	150-T1688	150-T1688
B M5 x 12mm pan phl screw	4	520-1027	520-1027	520-1027
C M5 X 25mm pan phl screw	4	520-9543	520-9543	520-9543
D M6 x 12mm pan phl screw	4	520-1128	520-1128	520-1128
E M6 x 25mm pan phl screw	4	520-1208	520-1208	520-1208
F M8 x 12mm pan phl screw	4	520-9571	520-9571	520-9571
G M8 x 25mm pan phl screw	4	520-1031	520-1031	520-1031
H M5/M4/M6 multi washer	4	580-1398	580-1398	580-1398
I 1/4"spacer	4	540-1059	540-1059	540-1059
J M5 x 20mm skt screw	2	520-1065	520-1065	520-1065
K 4mm allen wrench	1	560-9646	560-9646	560-9646
L front cover BLK front cover SLV	1	150-P1579P 150-4579P	151-P1816 151-4816	150-P1580P 150-4580P
M #14 x 2.5" wood screw	4	5S1-015-C03	5S1-015-C03	5S1-015-C03
N adaptor bracket	2	150-T1682	150-T1682	150-T1682
O power strip	1	600-0370	600-0370	600-0370
P cable tie	6	560-1756	560-1756	560-1756
Q concrete anchor (not used)	4	590-0320	590-0320	590-0320



A (1)
back assembly



L (1)
front cover





1

▲ WARNING

ENG - When installing Peerless wall mounts on a wood stud wall covered with gypsum board (drywall), verify that the wood studs are a minimum of 2" x 4" nominal size. Do not install over gypsum board thicker than 5/8".




1-1



ENG Use stud finder to locate and mark stud center lines.



1-2

KIL740, KIL742, KIL743	XX = 43.25", YY = 27.5"
KIL746, KIL747, KIL748	XX = 48.25", YY = 30.25"
KIL749, KIL755	XX = 55.75", YY = 33.75"





1-3

ENG Level wallplate. Mark mounting holes on stud.




1-4

ENG Drill mounting holes into supporting surface (2.5" (64 mm) minimum depth required).






1-5




1-6

ENG Level wallplate. Install using wood screws provided.






2

ENG Center adapter brackets vertically on back of screen.




3

ENG If there is interference on the back of the display with the adapter bracket, use the spacers provided. The depth of the spacers will need to be added to the depth of the display when determining if they will fit within the kiosk.




4




5


ENG Note: Mounting Arm swings out to access adapter brackets and behind display




6





7



8



9



ENG This page intentionally left blank.

ENG This page intentionally left blank.

ENG This page intentionally left blank.

ENG Warranty
ITL Garanzia

ESP Garantía
ČES Záruka

FRN Garantie
SLK Záruka

DEU Garantie
POR Garantia

NEL Garantie
TÜR Garanti

www.peerless-av.com/warranty

peerless-AV[®]

Peerless-AV

2300 White Oak Circle
Aurora, IL 60502
Email: tech@peerlessmounts.com
Ph: (800) 865-2112
Fax: (800) 359-6500
www.peerless-av.com

© 2020, Peerless Industries, Inc.

Peerless-AV Europe

Unit 3 Watford Interchange,
Colonial Way, Watford, Herts,
WD24 4WP, United Kingdom
Customer Care
44 (0) 1923 200 100
www.peerless-av.com

© 2020, Peerless Industries, Inc.

Peerless-AV América Latina

Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo N.L., México 66062
Servicio al Cliente
01-800-849-65-77
www.peerless-av.com

© 2020, Peerless Industries, Inc.