



A CSW Industrials Company

PRODUCT DATA SHEET

RECTORSEEK™ LOW-TEMP Leak Locator

Description

RectorSeek™ Low-Temp is designed to detect leaks in colder temperature ranges (from -35° F to +200° F) on pipe and tank systems that contain gases. DO NOT use on oxygen systems.

Instructions

1. Apply leak locator directly on pressurized joint or seam to be tested.
2. Bubbles will appear at location of leaking gas.
3. After testing, wipe off and allow to air dry.

For additional technical information, call Toll Free 1-800-231-3345.

Applications

- RectorSeek™ Low-Temp is formulated for use on all types of pipe, tubing, valves, cylinders, tanks, pressure vessels, condenser/evaporator coils, refrigeration coils, and many other similar applications*. Can be used with freons and ammonia.
- DO NOT use RectorSeek™ Low-Temp for oxygen leaks.

*Consult manufacturers for compatibility issues.

Characteristics | Features

- Longer bubbling action provides longer inspection periods
- For use at temperatures from -35° F to +200° F
- Easy to apply without any waste

Packaging



Code	Size	Qty. per Case	Lbs. per Case	Cubic Ft per Case
61273	Gallon (3.8 L)	4 Bottles	36	1.21

RECTORSEEK™ LOW-TEMP

Leak Locator

Specifications

Wt/Gal @ 77°F	8.8 lbs./gal.
Flash Point SETA CC	None
Color	Red
Shelf Life	2 years

Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances.

Precautions

FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT, CALL CHEMTREC-DAY OR NIGHT 1-800-424-9300.

Do not take internally. May be harmful if swallowed in large quantities. May cause mild eye or skin irritation. Wear adequate protective gear and clothing. Avoid contact with eyes and skin. Wash after handling. **FIRST AID:** For any overexposure, get immediate medical attention after first aid is given. **EYES** - Flush 15 minutes with clean water. **SKIN** - Wash with soap and water. **INGESTION** - Only if conscious, give large amounts of water and INDUCE VOMITING. **FIRE AND SPILLS:** For fire, use water fog, CO₂, foam or dry chemicals. Wipe up spills to prevent footing hazard. **STORAGE AND HANDLING:** Keep container closed when not in use. Do not reuse empty container. **KEEP OUT OF REACH OF CHILDREN.**

For additional information, refer to Safety Data Sheet.

Limited Warranty

RectorSeal, LLC makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RectorSeal, LLC. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal, LLC shall not be liable for incidental or consequential damages.

Manufactured by

RectorSeal, LLC

2601 Spenwick Drive • Houston, TX 77055, USA • 800-231-3345 • Fax 800-441-0051 • rectorseal.com

A CSW Industrials Company. RectorSeal, the logos and other trademarks are property of RectorSeal, LLC, its affiliates or its licensor's and are protected by copyright, trademark and other intellectual property laws, and may not be used without permission. RectorSeal reserves the right to change specifications without prior notice. ©2020 RectorSeal. All rights reserved. R50489-0720